

## Product data sheet

### Characteristics

# A9MEM3210

IEM3210 energy meter, Acti9, CT - 1 pulse O - MID



### Main

Range	Acti9
Range of product	Acti9 iEM3000
Device short name	iEM3210
Product or component type	Energy meter

### Complementary

Poles description	3P 1P + N 3P + N
Type of measurement	Active energy
Device application	Partial meter Sub billing
Accuracy class	Class 0.5S active energy conforming to IEC 62053-22 Class 0.5S active energy conforming to IEC 61557-12 Class C active energy conforming to EN 50470-3
Input type	External CT 1 A or 5 A
[In] rated current	5 A 1 A
Rated voltage	100...277 V 173...480 V
Network frequency	50 Hz 60 Hz
Technology type	Electronic
Display type	LCD display
Sampling rate	32 samples/cycle
Measurement current	1...32767000 mA
Maximum value measured	99999999 MWh
Communication port protocol	-
Communication port support	-
Local signalling	Green indicator light: power ON Yellow flashing LED: accuracy checking
Number of inputs	0
Number of outputs	1 pulse
Mounting mode	Clip-on
Mounting support	DIN rail
Connections - terminals	Current circuit: screw terminals 6 mm <sup>2</sup> cable(s) Voltage circuit: screw terminals 2.5 mm <sup>2</sup> cable(s)
Overvoltage category	III

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Standards	BS EN 61557-12:2021 IEC 61557-12:2021 EN 61557-12:2021 BS EN 61326-1 IEC 61326-1 EN 61326-1 BS EN 62052-11:2020 IEC 62052-11:2020 EN 62052-11:2020 BS EN 62053-21 IEC 62053-21 EN 62053-21 BS EN 62052-22 IEC 62053-22:2020 EN 62052-22 BS EN 62052-23 IEC 62053-23:2020 EN 62052-23 BS EN 62052-31:2015 IEC 62052-31:2015 EN 62052-31:2015 BS EN 61010-1:2010 EN 61010-1:2010 IEC 61010-1:2010 UL 61010-1:2010 BS EN 61010-2-30 IEC 61010-2-30 EN 61010-2-30 UL 61010-2-30 BS EN 50470-3 EN 50470-3 BS EN 50470-1 EN 50470-1 ANSI C12.20
-----------	--

Product certifications	CE conforming to IEC 61010-1 (safety)[RETURN]CE conforming to EN 61557-12 (power monitor)[RETURN]CE conforming to EN/IEC 61326-1 (EMC)[RETURN]UKCA conforming to BS EN 61010-1 (safety)[RETURN]UKCA conforming to BS EN 61557-12 (power monitor)[RETURN]UKCA conforming to BS EN 61326-1 (EMC)[RETURN]CULus conforming to UL 61010-1 (safety)[RETURN]CULus conforming to EN 61010-1 (safety)[RETURN]EAC conforming to EN 50470-3 (sub-meter)[RETURN]RCM conforming to EN 62052 (sub-meter)[RETURN]KZ conforming to EN 50470-3 (sub-meter)[RETURN]METAS conforming to EN 50470-1 (sub-meter)[RETURN]MID conforming to EN 50470-3 (sub-meter)[RETURN]MID conforming to EN 50470-1 (sub-meter)[RETURN]NMI conforming to NMI M 6-1
------------------------	--

## Environment

IP degree of protection	IP40 front panel: conforming to IEC 60529 IP20 body: conforming to IEC 60529
Pollution degree	2
Relative humidity	5...95 % at 50 °C
Ambient air temperature for operation	-25...70 °C - IEC
Ambient air temperature for storage	-40...85 °C
Operating altitude	< 2000 m
Colour	White
9 mm pitches	10
Width	90 mm
Height	95 mm
Depth	69 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	9.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	256 g
Unit Type of Package 2	S03
Number of Units in Package 2	30

Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	10616 g
Unit Type of Package 3	P12
Number of Units in Package 3	720
Package 3 Height	80 cm
Package 3 Width	120 cm
Package 3 Length	110 cm
Package 3 Weight	263784 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------