

## Product data sheet

### Characteristics

# A9N26500

## Overvoltage release iMSU - threshold 255V to 400V



### Main

Range of product	Acti 9 Prodis Clario Librio
Product or component type	Overvoltage release
Device short name	MSU
[Uc] control circuit voltage	230 V AC 50/60 Hz
Threshold tripping voltage	255 V 275 V 3...15 s 300 V 1...5 s 350 V 0.25...0.75 s 400 V 0.07...0.2 s
9 mm pitches	2

### Complementary

Range compatibility	Acti 9 iDPN Acti 9 C120 Acti 9 C40 Acti 9 C60H-DC Acti 9 C60NA-DC Acti 9 C60PV-DC Acti 9 DPN Vigi Acti 9 DT40 Acti 9 ID C40 Acti 9 IDc Acti 9 ITG40 Acti 9 ID Acti 9 DPN
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	73.5 mm
Net weight	66 g
Colour	White
Connections - terminals	Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm <sup>2</sup> - flexible Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule Screw clamp terminal (bottom) - 1 cable(s) 0.5...2.5 mm <sup>2</sup> - rigid
Wire stripping length	9 Mm 10 mm for bottom connection
Tightening torque	1 N.m bottom
Compatibility code	MSU

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	EN 50550
Quality labels	CE
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	74 g
Package 1 Height	2.8 cm
Package 1 width	8 cm
Package 1 Length	9.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Weight	656 g
Package 2 Height	10 cm
Package 2 width	10 cm
Package 2 Length	27 cm
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Weight	6.406 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------