


## Product data sheet

### Characteristics

# A9MEM1570

energy sensor, PowerTag Flex 63A 3P+N top and bottom position



### Main

Range of product	PowerLogic
Product name	PowerTag A9 F63
Product or component type	Energy sensor
Poles	3P + N
Maximum current [I <sub>max</sub> ]	63 A
[I <sub>b</sub> ] basic current	10 A
Starting current	40 mA
Saturation current	130 A
Product specific application	Cost allocation Load monitoring Overload alarm Circuit monitoring Energy management
Concentrator compatibility	Acti9 Smartlink SI B Acti9 Smartlink SI D Acti9 PowerTag Link C Acti9 PowerTag Link Acti9 PowerTag Link HD Harmony Hub
Range compatibility	Vigi DT40 Vigi iC40 Vigi iDT40 Vigi N40 Vigi C40 Vigi iC60 Acti 9 iDD40 Acti 9 iDD40 XA Acti 9 iCV40 XA Vigi iDPN Acti 9 iCV40 Vigi iTG40 Vigi iCG40
Type of measurement	Voltage Active energy Active power Current Power factor
Accuracy class	Class 1 current conforming to IEC 61557-12 Class 0.5 voltage conforming to IEC 61557-12 Class 1 active power conforming to IEC 61557-12 Class 1 active energy conforming to IEC 61557-12 Class 1 power factor conforming to IEC 61557-12
Mounting location	Top or bottom
Mounting support	On circuit breaker
Product destination	Switchboard
Event management	Voltage loss with measured current at voltage loss
Transmission support medium	Radio frequency 2.4...2.4835 GHz conforming to IEEE 802.15.4
Maximum emission power	10 mW

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Complementary

Mounting mode	By screws (terminals)
Electrical connection (voltage sensing & power supply)	Wires with cable end
Cable cross section	1 rigid cable 1.5...16 mm <sup>2</sup> 2 stranded cable 1.5...2.5 mm <sup>2</sup> 2 rigid cable 1.5...2.5 mm <sup>2</sup> 1 stranded cable 1.5...16 mm <sup>2</sup>
Cable length	0.25 m
Supply voltage	220...240 V AC, +/- 20 %, between phase and neutral 380...415 V AC, +/- 20 %, between phases
Network frequency	50 Hz 60 Hz
Maximum power consumption	2 VA
Standards	IEC 61557-12 IEC 61010-1 IEC 61010-2-030 IEC 61326-1 ETSI EN 300 328
Height	Sensor element: 20 mm
Width	Sensor element: 54 mm
Depth	Sensor element: 46.6 mm
Net weight	40 g
Colour	White (RAL 9003)

## Environment

Quality labels	CE
Directives	2014/53/EU - radio equipment directive
Operating altitude	0...2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C
Overvoltage category	III conforming to IEC 61010-1
Measurement category	Category III conforming to IEC 61010-2-030
IP degree of protection	IP20 conforming to IEC 60529
IK degree of protection	IK05
Pollution degree	3
Relative humidity	0...95 % at 45 °C conforming to IEC 60721-3-3
Vibration resistance	3M4 conforming to IEC 60721-3-3
Environmental characteristics	Dustproof class 3S3 conforming to IEC 60721-3-3 Salt mist class 3C2 conforming to IEC 60721-3-3

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins