

Product data sheet

Characteristics

A9MEM2000T

Acti9, Modular single phase power meter
iEM2000T - 230V - 40A without display



Main

Range	Acti9
Family	Acti9 iEM2000
Device short name	iEM2000T
Product or component type	Energy meter

Complementary

Poles description	1P + N
Type of measurement	Active power
Device application	Sub billing
Accuracy class	Class 1 active energy conforming to IEC 62053-21
Input type	Direct input
Maximum current [I _{max}]	40 A
[I _b] basic current	5 A
Rated current	40 A
Rated voltage	230 V +/- 20 %
Network frequency	60 Hz 50 Hz
Frequency measurement range	48...62 Hz
Technology type	Electronic
Display type	Without display
Sampling rate	32 samples/cycle
Measurement current	0.25...40 A
Display digits	0
Communication port protocol	-
Communication port support	-
Local signalling	Green indicator light: power ON Yellow indicator light: metering and activity 3200 p/kWh
Digital inputs	0
Digital outputs	1 pulse energy monitoring:
Output voltage	5...35 V DC@20 mA
Impulse duration	120 ms
Maximum power consumption in VA	10 VA at 240 V AC
Mounting mode	Clip-on
Mounting support	DIN rail
Connections - terminals	Power circuit: tunnel type terminals (bottom) 1 10 mm ² cable(s) Remote transfer: tunnel type terminals (top) 1 4 mm ² cable(s)
Tightening torque	Power circuit: 1.2 N.m Remote transfer: 0.8 N.m

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Standards	IEC 61557-12 IEC 62053-21
Product certifications	CE







Environment

IP degree of protection	IP40 front panel: conforming to IEC 60529 IP20 casing:
Ambient air temperature for operation	-25...65 °C -20...55 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	< 2000 m
Relative humidity	0...95 % at 55 °C
Colour	White
9 mm pitches	2
Width	18 mm
Height	96.5 mm
Depth	69 mm
Net weight	0.073 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	112.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	38
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.982 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------