

Product data sheet

Characteristics

A9MEM3110

iEM3110 energy meter - 63 A - 1 pulse O - MID



Main

Range	Acti 9
Range of product	Acti 9 iEM3000
Device short name	iEM3110
Product or component type	Energy meter

Complementary

Poles description	3P 1P + N 3P + N
Type of measurement	Active energy
Device application	Partial meter Sub billing
Accuracy class	Class 1 active energy conforming to IEC 62053-21 Class 1 active energy conforming to IEC 61557-12 Class B active energy conforming to EN 50470-3
Input type	Direct input
[In] rated current	63 A
Rated voltage	100...277 V 173...480 V
Network frequency	60 Hz 50 Hz
Technology type	Electronic
Display type	LCD display
Sampling rate	32 samples/cycle
Measurement current	0...63 A
Maximum value measured	99999999.9 kWh
Communication port protocol	-
Communication port support	-
Local signalling	Green indicator light: power ON Yellow flashing LED: accuracy checking
Number of inputs	0
Number of outputs	1 pulse
Mounting mode	Clip-on
Mounting support	DIN rail
Connections - terminals	Screw terminals 16 mm ² cable(s)
Overvoltage category	III

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Standards	IEC 62053-21 IEC 61036 IEC 62053-23 UL 61010-1 IEC 61557-12 IEC 61010
Product certifications	CE conforming to IEC 61010 (safety) CE conforming to EN 61557-12 (power monitor) CE conforming to IEC 61326-1 (EMC) CULus conforming to UL 61010 (safety) CULus conforming to ANSI C12.20 (sub-meter) EAC (sub-meter) RCM conforming to NMI M 6-1 (sub-meter) UL MID conforming to EN 50470-3 (sub-meter) MID conforming to EN 62052 (sub-meter)




Environment

IP degree of protection	IP40 front panel: conforming to IEC 60529 IP20 body: conforming to IEC 60529
Pollution degree	2
Relative humidity	5...95 % at 50 °C
Ambient air temperature for operation	-25...55 °C - MID -25...60 °C - NMI -25...60 °C - IEC
Ambient air temperature for storage	-40...85 °C
Operating altitude	< 2000 m
Colour	White
9 mm pitches	10
Width	90 mm
Height	95 mm
Depth	69 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	435.0 g
Package 1 Height	8 cm
Package 1 width	9.5 cm
Package 1 Length	10.5 cm
Unit Type of Package 2	S03
Number of Units in Package 2	30
Package 2 Weight	13526.0 g
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P12
Number of Units in Package 3	720
Package 3 Weight	333624.0 g
Package 3 Height	120 cm
Package 3 width	110 cm
Package 3 Length	80 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------