

Product data sheet

Characteristics

A9MEM3255-NMI

Acti9, IEM3255 energy meter - CT - Modbus - 1 digital I - 1 digital O - multi-tariff - NMI

Main

Range	Acti9
Range of product	Acti9 iEM3000
Device short name	iEM3255
Product or component type	Energy meter

Complementary

Poles description	3P + N 1P + N 3P
Type of measurement	Active and reactive energy Active and reactive power Current Voltage
Metering type	Active, reactive, apparent energy (signed, four quadrant)
Device application	Multi-tariff Partial meter Sub billing
Accuracy class	Class 0.5S active energy conforming to IEC 62053-22 Class 0.5S active energy conforming to IEC 61557-12 Class C active energy conforming to EN 50470-3
Input type	External CT 1 A or 5 A
[In] rated current	5 A 1 A
Rated voltage	100...277 V 173...480 V
Network frequency	60 Hz 50 Hz
Technology type	Electronic
Display type	LCD display
Sampling rate	32 samples/cycle
Measurement current	1...32767000 mA
Maximum value measured	99999999 MWh
Tariff input	Tariff (4)
Communication port protocol	Modbus RTU at 9.6, 19.2 and 38.4 kbauds even/odd or none, insulation 4000 V
Communication port support	Screw terminal block: RS485
Local signalling	Green indicator light: power ON Yellow flashing LED: accuracy checking Alarm: overload Yellow indicator light: communications are active on the Modbus port (Modbus)
Number of inputs	1 digital 0...5 V/11...40 V 24 V DC
Number of outputs	1 digital (static)
Output voltage	5...40 V DC@50 mA
Mounting mode	Clip-on

Mounting support	DIN rail
Connections - terminals	Current circuit: screw terminals 6 mm ² cable(s) Voltage circuit: screw terminals 2.5 mm ² cable(s)
Overvoltage category	III
Standards	IEC 61036 IEC 62053-23:2020 IEC 61010 IEC 62053-22:2020 IEC 61557-12:2021
Product certifications	CE conforming to IEC 61010 (safety) CE conforming to EN 61557-12 (power monitor) CE conforming to IEC 61326-1 (EMC) CULus conforming to UL 61010 (safety) CULus conforming to ANSI C12.20 (sub-meter) EAC (sub-meter) RCM ACMA NMI conforming to NMI M 6-1 (sub-meter)

Environment

IP degree of protection	IP40 front panel: conforming to IEC 60529 IP20 body: conforming to IEC 60529
Pollution degree	2
Relative humidity	5...95 % at 50 °C
Ambient air temperature for operation	-25...70 °C - IEC
Ambient air temperature for storage	-40...85 °C
Operating altitude	< 2000 m
Colour	White
9 mm pitches	10
Width	90 mm
Height	95 mm
Depth	69 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	9.8 cm
Package 1 Length	10.6 cm
Package 1 Weight	378.0 g