

Product data sheet

Characteristics

A9N18423

Miniature circuit breaker (MCB), Acti9 C120H, 3P, 63A, B curve, 15000A (IEC/EN 60898-1), 15kA (IEC/EN 60947-2)



Main

| | |
|---------------------------|---|
| Range of product | C120 |
| Range | Acti9 |
| Product name | C120 |
| Product or component type | Miniature circuit-breaker |
| Device short name | C120H |
| Device application | Distribution |
| Poles description | 3P |
| Number of protected poles | 3 |
| [In] rated current | 63 A at 30 °C |
| Network type | AC |
| Trip unit technology | Thermal-magnetic |
| Curve code | B |
| Breaking capacity | 15000 A Icn at 230...400 V AC 50/60 Hz conforming to EN/IEC 60898-1 10 KA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 KA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 30 KA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at <= 375 V DC conforming to EN/IEC 60947-2 |
| Suitability for isolation | Yes conforming to IEC 60947-2 |

Complementary

| | |
|--|---|
| Network frequency | 50/60 Hz |
| [Ue] rated operational voltage | <= 375 V DC 380...415 V AC 50/60 Hz 220...240 V AC 50/60 Hz 440 V AC 50/60 Hz 230...400 V AC 50/60 Hz |
| Magnetic tripping limit | 3...5 x In |
| [Ics] rated service breaking capacity | 7500 A 50 % conforming to EN/IEC 60898-1 - 230...400 V AC 50/60 Hz 5 KA 50 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 15 KA 50 % conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 7.5 KA 50 % conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 15 KA 100 % conforming to EN/IEC 60947-2 - <= 375 V DC |
| Limitation class | 3 conforming to EN/IEC 60947-2 |
| [Ui] rated insulation voltage | 500 V AC 50/60 Hz conforming to EN/IEC 60947-2 |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to EN/IEC 60947-2 |
| Contact position indicator | Yes |
| Control type | Toggle |
| Local signalling | ON/OFF indication |
| Mounting mode | Clip-on |
| Mounting support | 35 mm symmetrical DIN rail |
| Comb busbar and distribution block compatibility | YES |

| | |
|--------------------------|---|
| 9 mm pitches | 9 |
| Height | 81 mm |
| Width | 81 mm |
| Depth | 73 mm |
| Net weight | 0.615 kg |
| Colour | White |
| Mechanical durability | 20000 cycles |
| Electrical durability | 10000 cycles conforming to IEC 60947-2 |
| Connections - terminals | Tunnel type terminals 1...50 mm ² rigid Tunnel type terminals 1.5...35 mm ² flexible |
| Wire stripping length | 15 mm |
| Tightening torque | 3.5 N.m |
| Earth-leakage protection | Separate block |




Environment



| | |
|---------------------------------------|----------------------------------|
| Standards | EN/IEC 60947-2 EN/IEC 60898-1 |
| Product certifications | EAC |
| IP degree of protection | IP20 conforming to IEC 60529 |
| Pollution degree | 3 conforming to IEC 60947-2 |
| Overvoltage category | IV |
| Tropicalisation | 2 conforming to IEC 60068-1 |
| Relative humidity | 95 % at 55 °C |
| Operating altitude | 2000 m |
| Ambient air temperature for operation | -30...60 °C |
| Ambient air temperature for storage | -40...70 °C |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7.5 cm |
| Package 1 Width | 8 cm |
| Package 1 Length | 9 cm |
| Package 1 Weight | 565 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 4 |
| Package 2 Height | 8.5 cm |
| Package 2 Width | 9 cm |
| Package 2 Length | 33 cm |
| Package 2 Weight | 2.321 kg |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 24 |
| Package 3 Height | 30 cm |
| Package 3 Width | 30 cm |
| Package 3 Length | 40 cm |
| Package 3 Weight | 14.357 kg |

Offer Sustainability

| | |
|--------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |

| | |
|----------------------------|---|
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|
