

## Product data sheet

### Characteristics

# A9XAH457

Acti9 - comb busbar - 3L+N with Aux - 18 mm pitch - 57 modules - 100A



#### Main

Range	Acti9
Product or component type	Comb busbar
Mounting mode	Horizontal
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	57

#### Complementary

Number of ways	12 ways Aux + N + 3 L
Poles configuration for 1 way	1 x 3P + N 1 x 4P
Connection pitch	18 mm
Connector type	Tooth
Distance between way	81 mm
Marking	N L1 L2 L3
Insulation	Insulated
Device presentation	Cuttable
Provided equipment	Set of 10 end piece
[Ie] rated operational current	100 A at 40 °C
[Ue] rated operational voltage	415 V AC
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-2
Mounting location	Top or bottom on tunnel type terminals Top or bottom on double terminal
9 mm pitches	114
Width	1000 mm
Colour	White (RAL 9003)
Range compatibility	Acti 9 (Acti9 iC60) Acti 9 (Acti9 iK60) Acti 9 (Acti9 iLD) Acti 9 (Acti9 iLD K) Acti 9 (Acti9 iSW) Acti 9 (Acti9 iSW-NA) Multi 9 (Multi 9 C60)

#### Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	960 °C ( 30 s ) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.6 cm
Package 1 Width	9 cm
Package 1 Length	107 cm
Package 1 Weight	720 g
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	5.6 cm
Package 2 Width	9 cm
Package 2 Length	107 cm
Package 2 Weight	3.606 kg
Unit Type of Package 3	P12
Number of Units in Package 3	135
Package 3 Height	112 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	109.362 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------