


## Product data sheet

### Characteristics

# A9N18573

Acti 9 C120, earth leakage add-on block, 2P,  
300 mA, class A



### Main

Product or component type	Add-on residual current devices
Device short name	Vigi C120
Poles description	2P
[In] rated current	125 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A

### Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	230...415 V AC 50/60 Hz
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2
Mounting mode	Clip-on
Mounting support	35 mm symmetrical DIN rail
Electrical connection to mcb	By screws
9 mm pitches	7
Height	95 mm
Width	117 mm
Depth	73 mm
Net weight	0.325 kg
Colour	White
Mechanical durability	20000 cycles
Connections - terminals	Tunnel type terminals 1...35 mm <sup>2</sup> flexible Tunnel type terminals 1...50 mm <sup>2</sup> rigid
Wire stripping length	15 mm
Tightening torque	3.5 N.m

### Environment

Standards	EN 61009 IEC/EN 61009-2-1
IP degree of protection	IP20
Pollution degree	3 conforming to IEC 60947-2
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...60 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.300 cm
Package 1 Width	13.500 cm
Package 1 Length	13.500 cm
Package 1 Weight	372.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.616 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------