

Product data sheet

Characteristics

A9XAH657

Acti9 - comb busbar - 3L balanced with Aux -
18 mm pitch - 57 modules



Main

Range	Acti 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	57

Complementary

Number of ways	38 ways Aux + N + L
Poles configuration for 1 way	1 x 1P
Connection pitch	18 mm
Connector type	Tooth
Distance between way	27 mm
Marking	L1 L2 L3
Insulation	Insulated
Device presentation	Cuttable
Provided equipment	Set of 10 end piece
[Ie] rated operational current	100 A at 40 °C
[Ue] rated operational voltage	415 V AC
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-2
Mounting mode	Horizontal
Mounting location	Top or bottom on tunnel type terminals Top or bottom on double terminal
9 mm pitches	114
Width	1000 mm
Colour	White (RAL 9003)
Range compatibility	Acti9 iC60 Acti9 iK60 Acti9 iLD Acti9 iLD K Acti9 iSW Acti9 iSW-NA Multi 9 C60

Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	960 °C (30 s) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

Packing Units

Package 1 Weight	0.532 kg
Package 1 Height	0.150 dm
Package 1 width	0.300 dm
Package 1 Length	10.050 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------