

Product data sheet

Characteristics

A9N26924

Acti 9 - Auxiliary contact OC plus 1 SD and OF
ac dc



Main

Range of product	Prodis Acti 9 Librio Clario
Product or component type	OC contact
Device short name	OF
Signal contacts composition	1 C/O
[In] rated current	3 A: 380...415 V AC - 50/60 Hz 6 A: 220...240 V AC - 50/60 Hz 1 A: 130 V DC 1.5 A: 60 V DC 2 A: 48 V DC 6 A: 24 V DC
[Uc] control circuit voltage	24...415 V AC 50/60 Hz 24...130 V DC
9 mm pitches	1

Complementary

Range compatibility	Acti 9 DPN Vigi Acti 9 RCCB-ID Acti 9 C60H-DC Acti 9 C60PV-DC Acti 9 C40 Acti 9 ID C40 Acti 9 C120 Acti 9 DT40 Acti 9 DT60 Acti 9 IDc Acti 9 C120NA-DC Acti 9 iDPN Acti 9 ITG40 Acti 9 SW60-DC Acti 9 C60NA-DC
Mounting mode	Fixed
Mounting support	DIN rail
Height	85.3 mm
Width	9 mm
Depth	73.5 mm
Net weight	30 g
Colour	White
Connections - terminals	Clamp terminal (bottom) 2 cable(s) 1.5 mm ² - flexible Clamp terminal (bottom) 1 cable(s) 0.5...2.5 mm ² - rigid Clamp terminal (bottom) 2 cable(s) 1.5 mm ² - flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.m

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASEFA KEMA LCIE ASTA
IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	38 g
Package 1 Height	2 cm
Package 1 width	8 cm
Package 1 Length	9.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Weight	512 g
Package 2 Height	8.7 cm
Package 2 width	10 cm
Package 2 Length	26.5 cm
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Weight	5.088 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------