

Product data sheet

Characteristics

ACTFM1UF2LC12PS

Actassi for AsiaPacific, Fibre Optic Front
Adapters Plate with 12 x LC Dplx SM Adapters



Main

Range	Actassi
Product	Cover plate with adapters
Product destination	Fibre optic panel
Provided equipment	12 duplex single-mode adaptor for LC






Complementary

Material	PC
Fixing mode	Snap-in
Colour	Black
Width	120 mm
Height	35 mm
Depth	5.6 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.7 cm
Package 1 Width	4.7 cm
Package 1 Length	14 cm
Package 1 Weight	60.4 g
Unit Type of Package 2	CAR
Number of Units in Package 2	96
Package 2 Height	30 cm
Package 2 Width	29.9 cm
Package 2 Length	39.8 cm
Package 2 Weight	6.498 kg
Unit Type of Package 3	P12
Number of Units in Package 3	2304
Package 3 Height	102 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	168.462 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations