


Product data sheet

Characteristics

C325243

Acti9 MSC Chassis 3PH, 250A, 18mm for iC60 MCB, 24 poles, Dual Feed



Main

Range	Acti9
Device short name	MSC 18
Product or component type	Chassis
Device application	Distribution

Complementary

Range compatibility	Acti 9 (Acti9 Isobar B) distribution board
[In] rated current	250 A
Short-circuit withstand	25 kA 0.1 s
[Icw] rated short-time withstand current	25 kA
Number of ways	1 way (incomer) - 3P 24 ways (outgoer)
Outgoer Pole capacity	24 x 18 mm
Length	218 mm
Width	215 mm

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.0 cm
Package 1 Length	50.8 cm
Package 1 Weight	2.154 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China RoHS Regulation	 China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.