

## Product data sheet

### Characteristics

# C3DC323

## Acti9 MSC DC Chassis for iC60 1PH 250A 32P



### Main

Range	Acti 9
Device short name	MSC DC
Product or component type	Chassis
Device application	Distribution

### Complementary

Range compatibility	Acti9 Isobar A distribution board
[In] rated current	250 A
[Icw] rated short-time withstand current	25 kA
Short-circuit withstand	25 kA 0.1 s
Number of ways	1 way (incomer) - 2P 32 ways (outgoer)
Number of poles	32 x 18 mm
Width	215 mm
Length	290 mm
Busbar pitch	18 mm

### Packing Units

Package 1 Weight	4.899 kg
------------------	----------

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.