

Product data sheet

Characteristics

ACTFMSPTKIT

1U Fusion splice tray kit (max. 24-fiber)



Main

Range of product	Actassi
Product or component type	Optic splice cassette
Colour	Cassette: grey



Complementary

Range compatibility	19" fibre optic panel
Product destination	Empty fibre optic panel
Device composition	<ul style="list-style-type: none"> 1 cover 1 splice tray 2 insert 2 cable disc 1 cable gland 1 cable gland holder 4 screw 4 nut 30 heat shrink splice protector tube 4 ring
Number of port	24
Material	ABS (acrylonitrile butadiene-styrene)
Mounting type	<ul style="list-style-type: none"> By 2 screws with fibre patch panel By rivet with fibre patch panel with quick-fix function
Length	155.2 mm
Height	10 mm
Width	92.4 mm
Targeted region	<ul style="list-style-type: none"> Asia Pacific. Europe

Packing Units

Package 1 Weight	270.000 g
Package 1 Height	5.000 cm
Package 1 width	20.000 cm
Package 1 Length	20.000 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile