

Product data sheet

Characteristics

C3DC363

Acti9, MSC Chassis DC 2PH, 250A, 18mm for iC60 MCB & RCBO 36 poles, Dual Feed



Main

Range	Acti9
Device short name	MSC DC
Product or component type	Chassis
Device application	Distribution


Complementary

Range compatibility	Acti 9 (Acti9 Isobar A) distribution board
[In] rated current	250 A
[Icw] rated short-time withstand current	25 kA
Short-circuit withstand	25 kA 0.1 s
Number of ways	1 way (incomer) - 2P 36 ways (outgoer)
Number of poles	36 x 18 mm
Width	215 mm
Length	326 mm
Busbar pitch	18 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	71.12 cm
Package 1 Width	27.94 cm
Package 1 Length	10.16 cm
Package 1 Weight	4.899 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
China RoHS Regulation	 China RoHS Declaration