


Product data sheet

Characteristics

C3253034

Acti9, MSC Chassis 3PH, 400A, 18mm for iC60
MCB & RCBO, 30 poles, Dual Feed



Main

| | |
|---------------------------|--------------|
| Range | Acti9 |
| Device short name | MSC 18 |
| Product or component type | Chassis |
| Device application | Distribution |

Complementary

| | |
|--|---|
| Range compatibility | Acti 9 Acti9 Isobar B distribution board |
| [In] rated current | 400 A |
| [Icw] rated short-time withstand current | 25 kA |
| Number of ways | 1 way (incomer) - 3P 30 ways (outgoer) |
| Outgoer Pole capacity | 30 x 18 mm |
| Length | 272 mm |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.4 cm |
| Package 1 Width | 24.2 cm |
| Package 1 Length | 56.4 cm |
| Package 1 Weight | 3.22 kg |

Offer Sustainability

| | |
|-------------------|--|
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
|-------------------|--|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.