

Product data sheet

Characteristics

C3DC123

Acti9 MSC DC Chassis for iC60 1PH 250A 12P



Main

| | |
|---------------------------|--------------|
| Range | Acti 9 |
| Device short name | MSC DC |
| Product or component type | Chassis |
| Device application | Distribution |

Complementary

| | |
|-------------------------|---|
| Range compatibility | Acti9 Isobar A distribution board |
| [In] rated current | 250 A |
| Short-circuit withstand | 25 kA 0.1 s |
| Number of ways | 1 way (incomer) - 2P 12 ways (outgoer) |
| Number of poles | 12 x 18 mm |
| Width | 215 mm |
| Length | 110 mm |

Packing Units

| | |
|------------------|-----------|
| Package 1 Weight | 453.592 g |
|------------------|-----------|

Offer Sustainability

| | |
|-----------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| China RoHS Regulation |  China RoHS Declaration |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.