

Product data sheet

Characteristics

CAD32MD

TeSys Deca control relay - 3 NO + 2 NC - ≤
690 V - 220 V DC standard coil



Main

| | |
|---------------------------|---------------------|
| Range | TeSys TeSys Deca |
| Product name | TeSys CAD |
| Product or component type | Control relay |
| Device short name | CAD |
| Contact application | Control circuit |

Complementary

| | |
|---|--|
| Utilisation category | AC-14 AC-15 DC-13 |
| Pole contact composition | 3 NO + 2 NC |
| [Ue] rated operational voltage | ≤ 690 V AC 25...400 Hz |
| Control circuit type | DC standard |
| [Uc] control circuit voltage | 220 V DC |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947 |
| [Ith] conventional free air thermal current | 10 A (at 60 °C) |
| Irms rated making capacity | 140 A AC conforming to IEC 60947-5-1 250 A DC conforming to IEC 60947-5-1 |
| [Icw] rated short-time withstand current | 100 A - 1 s 120 A - 500 ms 140 A - 100 ms |
| Associated fuse rating | 10 A gG conforming to IEC 60947-5-1 |
| [Ui] rated insulation voltage | 600 V UL certified 600 V CSA certified 690 V conforming to IEC 60947-5-1 |
| Mounting support | Rail Plate |
| Connections - terminals | Screw clamp terminals 1 cable(s) 1...4 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 1...4 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 1...4 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 1...4 mm ² solid without cable end Screw clamp terminals 2 cable(s) 1...4 mm ² solid without cable end |
| Tightening torque | 1.2 N.M - on screw clamp terminals - with screwdriver Phillips No 2 1.2 N.M - on screw clamp terminals - with screwdriver flat Ø 6 mm 1.2 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 |
| Control circuit voltage limits | 0.1...0.25 U _c (-40...70 °C):drop-out DC 0.7...1.25 U _c (-40...60 °C):operational DC 1...1.25 U _c (60...70 °C):operational DC |
| Operating time | 53...72 ms coil energisation and NO closing 16...24 ms coil de-energisation and NO opening 47...63 ms coil energisation and NC opening 15...25 ms coil de-energisation and NC closing |
| Mechanical durability | 30 Mcycles |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|--------------------------------|--|
| Maximum operating rate | 180 cyc/mn |
| Time constant | 28 ms |
| Inrush power in W | 5.4 W (at 20 °C) |
| Hold-in power consumption in W | 5.4 W at 20 °C |
| Minimum switching voltage | 17 V |
| Minimum switching current | 5 mA |
| Non-overlap time | 1.5 Ms on energisation between NC and NO contact 1.5 ms on de-energisation between NC and NO contact |
| Insulation resistance | > 10 MOhm |
| Mechanical robustness | Shocks control relay open: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks control relay closed: 15 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations control relay open: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6 Vibrations control relay closed: 4 Gn, 5...300 Hz conforming to IEC 60068-2-6 |
| Height | 77 mm |
| Width | 45 mm |
| Depth | 93 mm |
| Net weight | 0.58 kg |

Environment

| | |
|---------------------------------------|--|
| Standards | BS 4794 EN 60947-5 IEC 60947-5-1 NF C 63-140 VDE 0660 IEC 60335-1 |
| Product certifications | UL CSA UKCA |
| IP degree of protection | IP2x front face conforming to VDE 0106 |
| Protective treatment | TH conforming to IEC 60068 |
| Ambient air temperature for operation | -40...60 °C 60...70 °C with derating |
| Ambient air temperature for storage | -60...80 °C |
| Operating altitude | 0...3000 m |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 502.0 g |
| Package 1 Height | 5 cm |
| Package 1 width | 9.2 cm |
| Package 1 Length | 11.2 cm |
| Unit Type of Package 2 | P06 |
| Number of Units in Package 2 | 120 |
| Package 2 Weight | 70.68 kg |
| Package 2 Height | 45 cm |
| Package 2 width | 80 cm |
| Package 2 Length | 60 cm |
| Unit Type of Package 3 | S02 |
| Number of Units in Package 3 | 15 |
| Package 3 Weight | 7.835 kg |
| Package 3 Height | 15 cm |
| Package 3 width | 30 cm |
| Package 3 Length | 40 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|