

## Product data sheet

### Characteristics

## CEF40-WE

Airflow, Ceiling Centrifugal Fan, 287mm, 35W,  
290Cubic m/Hr



### Main

Range of product	Airflow
Product brand	Clipsal

### Complementary

[Ue] rated operational voltage	240 V
Air flow	300 m3/h
Power consumption in W	35 W
[In] rated current	0.15 A full load

### Environment

IP degree of protection	IPx4
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	29.8 cm
Package 1 Width	37 cm
Package 1 Length	37.4 cm
Package 1 Weight	3.74 kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>