

Product data sheet

Characteristics

CH254234

Acti9, MSC Chassis 3PH, 400A, Hybrid 18/27mm for MCB & RCBO 42 poles, Dual Feed



Main

Range	Acti9
Device short name	MSC 18/27
Product or component type	Chassis
Device application	Distribution

Complementary

Range compatibility	Acti 9 Acti9 Isobar B distribution board
[In] rated current	400 A
[Icw] rated short-time withstand current	25 kA
Number of ways	1 way (incomer) - 3P 42 (outgoer)
Outgoer Pole capacity	30 x 18 mm 12 x 27 mm
Length	434 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.000 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.