

Product data sheet

Characteristics

CLITPDBLED2EM

Actassi, Clipsal - LED diffused batten light,
40W, 3800 lm, 4000K, IP20, 1200mm,
Emergency



Main

Range	Actassi
Product or component type	Batten light
Device application	Residential Commercial
Battery type	LiFePO4

Complementary

Operational power in W	45 W
Power factor	0.9
Light source	LED 40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	3800 lm
Bulb lifespan	50000 h
Colour temperature	4000 K
Autonomy	2 h
Charging time	16 h
Control type	Test button
Supply	Maintained
Device mounting	Surface
Mounting mode	By screws
IP degree of protection	IP20
Length	1230 mm
Width	80 mm
Height	85 mm
Distance between centers	945 mm
Net weight	1.8 kg

Environment

Colour rendering index	R _a =80
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...85 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	9.0 cm
Package 1 Length	126.0 cm
Package 1 Weight	2.6 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes