

Product data sheet

Characteristics

CLITPFLS20SENLED

Clipsal - Lighting, Floodlight LED, 20W, 4000K, 1800lm, with Sensor



Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting

Complementary

Type of installation	Outdoor
Device mounting	Surface
Total system power	20 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	1800 lm
Sensor detection angle	120°
Sensor detection range	12 m
Sensor time span	10 min
Colour rendering index	R _a =70
Bulb lifespan	30000 h
Colour temperature	4000 K
Beam angle	100 °
Electrical insulation class	Class I
Height	Body with trunion arm: 235 mm
Width	116 mm
Depth	29 mm
Net weight	0.75 kg
Cable length	0.9 m

Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	23.0 cm
Package 1 Width	6.0 cm
Package 1 Length	21.0 cm
Package 1 Weight	1.33 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	24.0 cm
Package 2 Width	40.4 cm
Package 2 Length	55.0 cm
Package 2 Weight	10.9 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	3-Years
----------	---------