


Product data sheet

Characteristics

CLP593011

Clipsal Wiser, Temperature/ Humidity Smart Sensor White



Main

Product brand	Clipsal
Range	Wiser
Concentrator compatibility	Wiser hub generation 1
Product or component type	Sensor
Mobile App name	Wiser by SE
Colour tint	White (RAL 9003)
Sensor type	Humidity sensor Temperature
Supply	Battery3 V / CR2450

Complementary

Device presentation	Complete product
Device mounting	Surface
Communication network type	Wireless Zigbee (2.4 GHz), 2.5 mW at < 50 m
Battery life	5 year(s)
Local signalling	1 orange LED blinking , function: battery needs replacing
Measurement range	10...95 % RH
Measurement temperature	-10...50 °C
Measurement signal interval	30 min 10 min 5 min 1 min
Fixing mode	By screws and dowels Adhesive tape
Depth	17.2 mm
Height	45 mm
Width	45 mm
Standards	EN/IEC 60730-2-9 EN/IEC 60730-2-13
Product certifications	CE[RETURN]Zigbee 3.0

Environment

Ambient air temperature for operation	-10...50 °C
Relative humidity	10...95 %
Operating altitude	<= 2000 m
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	5.2 cm
Package 1 Length	7.5 cm

Package 1 Weight	75.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.315 kg
Unit Type of Package 3	P06
Number of Units in Package 3	640
Package 3 Height	75.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	61.54 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information