

Product data sheet

Characteristics

CLP723419

Clipsal Wiser, IP Camera, Wi-Fi, Pan and Tilt Adjustment, Indoor, IP20



Main

Product brand	Clipsal
Range	Wiser
Concentrator compatibility	Wiser hub generation 1
Mobile App name	Wiser by SE
Product or component type	Camera
Device application	Surveillance
Colour tint	White

Complementary

[Us] rated supply voltage	5 V
Maximum supply current	2 A
Network type	DC
Power consumption in W	10 W
Communication network type	Wireless Zigbee (2.4 GHz), 2.5 mW at < 50 m
Integrated connection type	Micro USB port for power supply
Data storage equipment	Micro SD card, up to 128 GB
Communication port protocol	HTTPS DHCP DNS
Channel bandwidth support	20 MHz 40 MHz
Maximum number of supported devices	4 per network
Sensor type	CMOS Digital WDR (wide dynamic range)
Sensor size	1/2.9"
Pixel resolution	2 megapixel
Length	Lens: 4 mm
View angle horiz x vert	80° horizontal 40° vertical
Operating mode	Pan at 0...340 ° Tilt at -75...75 °
Device composition	8 infrared LED
Operating distance	7 m for IR LED
Audio system control module type	Full duplex
Audio video coding standard	H.264 MJPEG
Display resolution	1080 pixels
Transmission rate	1.2 Mbit/s
Camera frame rate	20 fps
Data recording	Event logs
Function available	Video motion detection Follow and track motion

Encryption protocol	AES 128 WPA-PSK WPA2-PSK
Material	Plastic
Type of installation	Indoor
Diameter	72.5 mm
Height	129 mm
Net weight	298 g

Environment

IP degree of protection	IP20
Ambient air temperature for operation	-10...45 °C
Ambient air temperature for storage	-20...60 °C
Relative humidity	95 % maximum
Product certifications	CE[RETURN]FCC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	18.3 cm
Package 1 Length	13.5 cm
Package 1 Weight	530.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.87 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	216
Package 3 Height	105.0 cm
Package 3 Width	114.0 cm
Package 3 Length	114.0 cm
Package 3 Weight	143.66 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins