

## Product data sheet

### Characteristics

# CLP724419

## IP camera, Wiser, IP56, Wi-Fi, pan and tilt adjustment, Outdoor, white



### Main

Product brand	Clipsal
Range	Wiser
Product or component type	Camera
Device application	Surveillance
Colour tint	White

### Complementary

[Us] rated supply voltage	12 V
Maximum supply current	1 A
Network type	DC
Power consumption in W	6 W
Integrated connection type	Micro USB port for power supply
Data storage equipment	Micro SD card, up to 128 GB
Communication network type	Wi-Fi - 2.4 GHz conforming to IEEE 802.11 b/g/n
Communication port protocol	HTTPS DHCP DNS
Channel bandwidth support	20 MHz 40 MHz
Maximum number of supported devices	4 per network
Sensor type	CMOS Digital WDR (wide dynamic range)
Sensor size	1/2.9"
Pixel resolution	2 megapixel
Length	Lens: 4 mm
View angle horiz x vert	80° horizontal 40° vertical
Operating mode	Pan at 0...340 ° Tilt at -75...75 °
Device composition	8 infrared LED
Operating distance	7 m for IR LED
Audio system control module type	Full duplex
Audio video coding standard	H.264 MJPEG
Display resolution	1080 pixels
Transmission rate	1.2 Mbit/s
Camera frame rate	20 fps
Data recording	Event logs
Function available	Video motion detection Follow and track motion

Encryption protocol	AES 128 WPA-PSK WPA2-PSK
Material	Plastic
Type of installation	Outdoor
Diameter	72.5 mm
Height	129 mm
Net weight	298 g

## Environment

IP degree of protection	IP56
Ambient air temperature for operation	-10...45 °C
Ambient air temperature for storage	-20...60 °C
Relative humidity	95 % maximum
Product certifications	CE FCC

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	428.0 g
Package 1 Height	8.5 cm
Package 1 width	18.3 cm
Package 1 Length	13.5 cm
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	5.22 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	PAL
Number of Units in Package 3	216
Package 3 Weight	92.45 kg
Package 3 Height	105 cm
Package 3 width	114 cm
Package 3 Length	114 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>