

Product data sheet

Characteristics

CCT15720

Acti9 - IHP - 1C digital time switch - 24 hours + 7 days



Main

Range of product	Acti9
Product name	Acti9 IHP
Device short name	IHP
Product or component type	Programmable digital time switch
Device application	Building
Battery type	Lithium
Number of channels	1
User language	English French Portuguese Italian German Spanish
Colour tint	White (RAL 9003)

Complementary

Product compatibility	Mechanical compatibility with electrical distribution comb busbars
Power consumption in VA	4 VA
Maximum switching current	10 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
[Ue] rated operational voltage	230 V AC +/- 10 % at 50/60 Hz
Accuracy	+/- 1 s/day 20 °C
Cycle duration	24 hours + 7 days
Maximum number of switchings	56
Minimum interval duration	1 min
Function available	Automatic winter/summer time changeover
Display type	Backlit LCD
Battery life	6 year(s)
Backup time	6 years time and program saving
Type of setting	Absence for holidays function
Connections - terminals	Screwless terminals
Mounting support	DIN rail
9 mm pitches	5
Width	45 mm
Height	85 mm
Depth	66 mm
Function	None
Absence for holidays	Yes
Time changeover	Automatic
Updated by	None
Compatibility code	IHP

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP20 B

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------