

Product data sheet

Characteristics

E01CNN32

Medilec, RCD Modules and Covers, 240V AC
32A 10mA RCD / MCB Module



Main

Range	Clipsal - Series E01 Medilec
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
[In] rated current	32 A
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Class AC

Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	240 V AC
Protection type	Short time short-circuit protection
Mounting support	DIN rail
Size	74 x 45 x 65 mm conforming to DIN 43880




Environment

Standards	AS/NZS 3190
Ambient air temperature for operation	-10...55 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	289 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes