

Product data sheet

Characteristics

CEF40-WE

Airflow, Ceiling Centrifugal Fan, 287mm, 35W, 290Cubic m/Hr



Main

Product brand	Clipsal
---------------	---------



Complementary

[Ue] rated operational voltage	240 V
Air flow	300 m3/h
Power consumption in W	35 W
[In] rated current	0.15 A full load

Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	29.8 cm
Package 1 Width	37 cm
Package 1 Length	37.4 cm
Package 1 Weight	3.74 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile