

Product data sheet

Characteristics

EGX150

Link 150 - ethernet gateway - 2 Ethernetport - 24 V DC and PoE



Main

Range	Enerlin'X
Product name	Link
Product or component type	Gateway
Device short name	Link150
Device application	Gateway
External supply	External supply: 19.2...26.4 V DC, <500 mA
PoE	Power supply device PoE conforming to IEEE 802.3af
Number of port	2
Communication gateway	Ethernet/fieldbus

Complementary

Current consumption	130 mA at 24 V DC via external supply (20 °C) 65 mA at 48 V DC via PoE (20 °C)
Maximum power consumption in W	15 W via PoE
Communication network type	Ethernet, Ethernet Modbus TCP/IP daisy chain even/odd or none parity, at 10/100 Mbit/s Ethernet, PoE 15W (Power over Ethernet) even/odd or none parity, at 10/100 Mbit/s Ethernet, FTP even/odd or none parity, at 10/100 Mbit/s Ethernet, HTTP even/odd or none parity, at 10/100 Mbit/s Ethernet, SNMP even/odd or none parity, at 10/100 Mbit/s Ethernet, Modbus TCP/IP even/odd or none parity, at 10/100 Mbit/s RS232, Modbus RTU, JBUS, PowerLogic (SY/MAX) even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds RS232, Modbus ASCII even/odd or none parity, at 2400, 4800, 9600, 19200, 38400, 56000 or 57600 bauds RS232, Modbus Serial line slave even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds RS485, Modbus RTU, JBUS, PowerLogic (SY/MAX) even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds RS485, Modbus ASCII even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds RS485, Modbus Serial line slave even/odd or none parity, at 2400, 4800, 9600, 19200 or 38400 bauds
Parity	Even/odd or none
Communication port protocol	Ethernet Modbus TCP/IP daisy chain, insulation 6 kV Modbus TCP/IP, insulation 6 kV Modbus RTU, JBUS, PowerLogic (SY/MAX), master - 2 or 4 wires, insulation 2.5 kV Modbus ASCII, master - 2 or 4 wires, insulation 2.5 kV Modbus RTU and ASCII, slave - 2 or 4 wires, insulation 2.5 kV
Communication port support	RJ45: Ethernet RJ45: RS232 RJ45: RS485
Number of inputs	0
Number of outputs	0
Connections - terminals	Power supply: screw terminal block (top) 0.2...1.5 mm ² cable(s) rigid Power supply: screw terminal block (top) 0.2...1.5 mm ² cable(s) flexible with cable end Power supply: screw terminal block (top) 0.2...1.5 mm ² cable(s) flexible without cable end

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Tightening torque	Power supply: 0.3 N.m flat screwdriver 3 mm
Wire stripping length	Power supply: 7 mm for top connector connection
Mounting mode	Clip-on
Mounting support	35 mm DIN rail
Product certifications	CULus FCC Class A CE RCM UL CUL
Standards	IEC 60950-1 UL 61010-2-201 UL 61010-1 CSA C22.2 No 60950-1 AS/NZS 60950-1 UL 60950-1 IEC 61000-6-2
Depth	72 mm
Height	105 mm
Width	71 mm
Net weight	175 g
Web services	Web server
Local signalling	LED: for Ethernet activity (ETH1) LED: for Ethernet activity (ETH2) LED: for module status LED: for network communication status (Net Status) LED: for communication (RS232) LED: for communication (RS485)
Compatibility code	EGX150

Environment

Relative humidity	5...95 % at 55 °C without condensation
IP degree of protection	IP40 (front panel (in enclosure)) IP30 (casing) IP20 (terminal block)
Mechanical robustness	Vibrations in operation: 1 Gn, 5 Hz...150 Hz conforming to IEC 60068-2-6 Vibrations de-energized: 1 Gn, 5 Hz...150 Hz conforming to IEC 60068-2-6 Shocks in operation: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks de-energized: 15 Gn for 11 ms conforming to IEC 60068-2-27 Jolts de-energized: 100 jolts/axle, 15 Gn for 6 ms conforming to IEC 60068-2-29 Free fall resistance: 1.2 m
Electromagnetic compatibility	Immunity for industrial environments conforming to EN 61000-6-2 Immunity for industrial environments conforming to CISPR 24 Conducted and radiated emissions conforming to FCC part 15 class B Conducted and radiated emissions conforming to EN 55022 Conducted and radiated emissions conforming to CISPR 22 Electrostatic discharge - test level: 8 kV air, 6 kV contact B conforming to EN 61000-4-2 Radiated RF fields - test level: 10 V/m, 80 MHz...1 GHz A conforming to EN 61000-4-3 Radiated RF fields - test level: 3 V/m, 1 MHz...3 GHz A conforming to EN 61000-4-3 Fast transients immunity test level 4 conforming to EN 61000-4-4 Fast transient bursts class 3 conforming to EN 61000-4-12 Surges - test level: level 4 B (1.2/50 µs) conforming to EN 61000-4-5 Conducted RF disturbances - test level: 10 V conforming to EN 61000-4-6 Conducted RF disturbances conforming to CISPR 11 Magnetic field at power frequency - test level: 30 A/m class 5 conforming to EN 61000-4-8 Voltage dips and interruptions immunity test - test level: 100 %, 20 ms B conforming to EN 61000-4-11 Voltage dips and interruptions immunity test - test level: 60 %, 200 ms B conforming to EN 61000-4-11 Voltage dips and interruptions immunity test - test level: 30 %, 500 ms conforming to EN 61000-4-11
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Pollution degree	2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	250 g
Package 1 Height	8.872 cm
Package 1 width	9.229 cm
Package 1 Length	12.366 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information