

Product data sheet

Characteristics

CH25303

Acti9 - MSC 18/27 hybrid Chassis - for iC60 - 3PH - 250A - 30P



Main

Range	Acti 9
Device short name	MSC 18/27
Product or component type	Chassis
Device application	Distribution

Complementary

Range compatibility	Acti9 Isobar B distribution board
[In] rated current	250 A
Short-circuit withstand	25 kA 0.1 s
[Icw] rated short-time withstand current	25 kA
Number of ways	1 way (incomer) - 3P 30 ways (outgoer)
Outgoer Pole capacity	6 x 27 mm 24 x 18 mm
Length	299 mm
Width	215 mm

Packing Units

Package 1 Weight	1.000 kg
Package 1 Height	1.000 dm
Package 1 width	1.000 dm
Package 1 Length	1.000 dm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China RoHS Regulation	 China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.