


## Product data sheet

### Characteristics

# CH25723

Acti9, MSC 18/27 hybrid Chassis - for iC60 -  
3PH - 250A - 72P



### Main

Range	Acti9
Device short name	MSC 18/27
Product or component type	Chassis
Device application	Distribution

### Complementary

Range compatibility	Acti 9 (Acti9 Isobar B) distribution board
[In] rated current	250 A
Short-circuit withstand	25 kA 0.1 s
[Icw] rated short-time withstand current	25 kA
Number of ways	1 way (incomer) - 3P 72 (outgoer)
Outgoer Pole capacity	12 x 27 mm 60 x 18 mm
Length	704 mm
Width	215 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	23.5 cm
Package 1 Length	99.5 cm
Package 1 Weight	5.571 kg

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.