

Product data sheet

Characteristics

EY56C310

Easy56 Switched Socket - 3 Pin - 10A - 250V



Main

Product name	Easy56
Product or component type	Switch and socket-outlet
Device short name	EY56C310
Plug, socket category	Low voltage
Poles description	1P + N + E
Control type	Rotary knob
Rotary handle padlocking	2 padlocks 8 mm
Network type	AC
Outlet standard deviation	Australian/New Zealand

Complementary

Mounting mode	Surface mounted
Plug, socket, control station shape	Straight
[In] rated current	10 A
Pin number	3 pins
Shape of pin	Flat
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Protection type	Without protection
Material	Polycarbonate
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals
Cable cross section	1.5...6 mm ²
Cable entry number	2 x M25 1 x M32
Net weight	0.82 kg
Height	203 mm
Width	101 mm
Depth	101 mm
Colour	Body: grey (RAL 7035) Rotary handle: dark grey

Environment

Standards	AS/NZS 3112 AS/NZS 3133
Quality labels	RCM
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	11.4 cm
Package 1 Width	10.4 cm
Package 1 Length	20.7 cm
Package 1 Weight	861 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	12
Package 2 Height	224 cm
Package 2 Width	360 cm
Package 2 Length	448 cm
Package 2 Weight	9.84 kg
Package 3 Height	100 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile