

Product data sheet

Characteristics

CLITPFLS100LED

Floodlight LED, 100W, 4000K, 9000lm, Black



Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting

Complementary

Type of installation	Outdoor
Device mounting	Surface
Total system power	100 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	9000 lm
Colour rendering index	R _a =70
Bulb lifespan	30000 h
Colour temperature	4000 K
Beam angle	100 °
Electrical insulation class	Class I
Height	Body with trunion arm: 260 mm
Width	357 mm
Depth	45 mm
Net weight	2.45 kg
Cable length	0.9 m

Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.278 kg
Package 1 Height	84 mm
Package 1 width	330 mm
Package 1 Length	414 mm

Contractual warranty

Warranty

3-Years
