

## Product data sheet

### Characteristics

# CLITPFLS100LED

## Floodlight LED, 100W, 4000K, 9000lm



### Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting

### Complementary

Type of installation	Outdoor
Device mounting	Surface
Total system power	100 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	9000 lm
Colour rendering index	R <sub>a</sub> =70
Bulb lifespan	30000 h
Colour temperature	4000 K
Beam angle	100 °
Electrical insulation class	Class I
Height	Body with trunion arm: 260 mm
Width	357 mm
Depth	45 mm
Net weight	2.45 kg
Cable length	0.9 m

### Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	33.0 cm
Package 1 Length	41.4 cm
Package 1 Weight	3.278 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	2
Package 2 Height	17.4 cm

Package 2 Width	34.6 cm
Package 2 Length	42.8 cm
Package 2 Weight	7.1 kg

### Contractual warranty

Warranty	3-Years
----------	---------