

Product data sheet

Characteristics

CLITPHBM2

LED Highbay 150W, 5000K, 18,500lm, IP65



Main

Range	Clipsal
Product name	TPHB Series
Product or component type	High bay light
Device application	Lighting
Type of installation	Indoor/outdoor
Market segment	Industrial buildings Commercial

Complementary

Environmental characteristic	Harsh environment
Light source	LED 150 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	18500 lm
Colour temperature	5000 K
Beam angle	120 °
Mounting mode	By hook
Provided equipment	Flex Plug
IP degree of protection	IP65
Electrical insulation class	Class I
Material	Die cast aluminium housing Acrylic lens
Width	360 mm
Diameter	360 mm
Product weight	4.0 kg

Environment

Total system power	150 W
Bulb lifespan	50000 h
Ambient air temperature for operation	-10...50 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	5.26 kg
Package 1 Height	220 mm
Package 1 width	415 mm
Package 1 Length	415 mm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration