

Product data sheet

Characteristics

EY56SW110LE

Easy 56 Switch - 1P - 10A - 250V - Less Enclosure



Main

Product name	Easy56
Device short name	EY56SW110LE
Product or component type	Switch
Poles description	1P
Network type	AC
Network frequency	50 Hz
Control type	Rotary knob
Rotary handle padlocking	2 padlocks
Handle colour	Grey

Complementary

[Ue] rated operational voltage	250 V AC 50 Hz
[Ithe] conventional enclosed thermal current	10 A
[Ie] rated operational current	10 A at 250 V
Connections - terminals	Screw terminals 1.5...6 mm ² - rigid or stranded
Height	101 mm
Width	101 mm
Net weight	0.191 kg
Colour	Body: grey (RAL 7035) Rotary handle: dark grey

Environment

Standards	AS/NZS 3133
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.