

Product data sheet

Characteristics

CLITPLP6

Clipsal - panel LED - with driver - 36W - 5000K
- IP20 - 1200X300mm - white



Main

Range	Clipsal
Product name	TPLP Series
Product or component type	Panel light
Device application	Lighting

Complementary

Type of installation	Indoor
Total system power	40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	3700 lm
Bulb lifespan	50000 h
Colour temperature	5000 K
Colour	White
Mounting mode	Ceiling
Light source	LED 36 W
Height	1195 mm
Width	295 mm
Depth	10 mm
Net weight	3.2 kg

Environment

IP degree of protection	IP20
Relative humidity	10...95 % non-condensing
Ambient air temperature for operation	-10...45 °C
Targeted country	Australia New Zealand

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	35 cm
Package 1 Length	125 cm
Package 1 Weight	3100 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration