

Product data sheet

Characteristics

CLITPWPLED2

Clipsal - LED weatherproof Batten - 40W - 5000K - IP65 - 1200mm



Main

Range	Clipsal
Product name	TPWP Series
Product or component type	Batten light
Device application	Lighting
Battery type	LiFePO4

Complementary

Type of installation	Outdoor
Total system power	40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	3800 lm
Bulb lifespan	50000 h
Colour temperature	5000 K
Mounting mode	Wall-mounted
Light source	LED 40 W
Autonomy	2 h
Charging time	16 h
Control type	Test button
Supply	Non-maintained
Focal length	900 mm
Height	90 mm
Width	140 mm
Length	1274 mm
Net weight	2.26 kg

Environment

IP degree of protection	IP65
IK degree of protection	IK08
Relative humidity	10...85 % non-condensing
Ambient air temperature for operation	-10...50 °C
Targeted country	Australia

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.01 kg
Package 1 Height	10 cm
Package 1 width	16 cm
Package 1 Length	123 cm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------