

Product data sheet

Characteristics

CLP5011WSZ

Clipsal Wiser, Micro Module Smart Switch 10 AX, 240 V, Grey



Main

Product brand	Clipsal
Range	Iconic
Product or component type	Connected switch
Concentrator compatibility	Wiser hub generation 1
Mobile App name	Wiser by SE

Complementary

Device presentation	Module
Technology type	Electronic
Load type	Dimmable LED lighting driver: 10 A LED lighting driver (non-dimmable): 10 A Electronic transformer: 10 A Medium voltage halogen lamp: 10 A Linear fluorescent ballast: 10 A Inductive: 6 A (cos phi =0.6) Resistive: 15 A Motor: 10 A
[Ue] rated operational voltage	220...240 V AC 50 Hz
Protection type	Over temperature protection Thermal protection
Colour tint	Grey
Surface finish	Matt
Control type	Push-button By mobile application
Software name	Wiser App
Technology type	Zigbee
Communication network type	Wireless (2.4 GHz), 2.5 mW at < 50 m
Wiring configuration	3-wire
Material	Plastic
Mounting support	Wall Installation box
Type of installation	Indoor installation

Environment

Relative humidity	5...90 % non-condensing
Standards	AS/NZS 60669.2.1 safety AS/NZS 60669.2.1 EMC AS/NZS 4268 radio

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	62.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.96 kg
Unit Type of Package 3	P06
Number of Units in Package 3	640
Package 3 Height	75.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	62.36 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information