

## Product data sheet

### Characteristics

# CLP501902

## Hub, Clipsal Wiser, Zigbee to IP Network

### Main

Range	Wiser
Product or component type	Hub
Device application	Zigbee/IP network interface
Colour tint	White

### Complementary

Mobile App name	Wiser by SE
Concentrator compatibility	Wiser hub generation 1
Communication network type	Wireless Zigbee (2.4 GHz), 2.5 mW at < 50 m
Port Ethernet	10/100BASE
Connector type	Connector(S)1 x micro USB port female for adaptor Connector(s)1 x 2-pin terminal block for 12 V DC power supply
Electrical connection	Cable, 0.25...1.5 mm <sup>2</sup> (terminal)
[Us] rated supply voltage	5 V DC, <1 A 12 V DC, <0.5 A
Realtime clock	With RTC-battery set
Local signalling	Indicator: 3 LEDs (white)
Width	86 mm
Height	86 mm
Depth	34 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	10...90 %
Environmental characteristic	Indoor use
IP degree of protection	IP20
Standards	EN 62368-1 IEC 62368-1
Product certifications	CE

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	18.7 cm
Package 1 Length	13.5 cm
Package 1 Weight	327 g
Unit Type of Package 2	S02
Number of Units in Package 2	8

Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.016 kg
Unit Type of Package 3	P12
Number of Units in Package 3	320
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	128 kg

### Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	No