

Product data sheet

Characteristics

CLP724419

IP Camera, Clipsal Wiser, Wi-Fi, Outdoor, IP56



Main

| | |
|----------------------------|------------------------|
| Product brand | Clipsal |
| Range | Wiser |
| Concentrator compatibility | Wiser hub generation 1 |
| Mobile App name | Wiser by SE |
| Product or component type | Camera |
| Device application | Surveillance |
| Colour tint | White |

Complementary

| | |
|-------------------------------------|---|
| [Us] rated supply voltage | 12 V |
| Maximum supply current | 1 A |
| Network type | DC |
| Power consumption in W | 6 W |
| Communication network type | Wireless Zigbee (2.4 GHz), 2.5 mW at < 50 m |
| Integrated connection type | Micro USB port for power supply |
| Data storage equipment | Micro SD card, up to 128 GB |
| Communication port protocol | HTTPS DHCP DNS |
| Channel bandwidth support | 20 MHz 40 MHz |
| Maximum number of supported devices | 8 per network |
| Sensor type | CMOS Digital WDR (wide dynamic range) |
| Sensor size | 1/2.7" |
| Pixel resolution | 2 megapixel |
| Length | Lens: 4 mm |
| View angle horiz x vert | 103° horizontal 54° vertical |
| Device composition | 8 infrared LED |
| Operating distance | 10 m for IR LED |
| Audio system control module type | Semi duplex |
| Audio video coding standard | H.264 MJPEG |
| Display resolution | 1080 pixels |
| Transmission rate | 1.2 Mbit/s |
| Camera frame rate | 15 fps |
| Data recording | Event logs |
| Function available | Video motion detection |
| Encryption protocol | AES 128 WPA-PSK WPA2-PSK |
| Material | Plastic |

| | |
|----------------------|----------|
| Type of installation | Outdoor |
| Diameter | 77 mm |
| Height | 149.7 mm |
| Net weight | 220 g |

Environment

| | |
|---------------------------------------|---------------|
| IP degree of protection | IP56 |
| Ambient air temperature for operation | -10...45 °C |
| Ambient air temperature for storage | -20...60 °C |
| Relative humidity | 95 % maximum |
| Product certifications | CE[RETURN]FCC |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 8.5 cm |
| Package 1 Width | 18.3 cm |
| Package 1 Length | 13.5 cm |
| Package 1 Weight | 435.0 g |
| Unit Type of Package 2 | S03 |
| Number of Units in Package 2 | 12 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 5.73 kg |
| Unit Type of Package 3 | PAL |
| Number of Units in Package 3 | 216 |
| Package 3 Height | 105.0 cm |
| Package 3 Width | 114.0 cm |
| Package 3 Length | 114.0 cm |
| Package 3 Weight | 123.14 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |