

## Product data sheet

### Characteristics

# E463P

## Extension Socket, Metal Clad, Multi Phase, 500V, 63A, 4 Round Pins

### Main

Range of product	E Wilco
Product brand	Clipsal

### Complementary

[In] rated current	63 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Material	Aluminium
Connections - terminals	Screw terminal
Plug, socket, control station shape	Straight
Duration	7 h

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.6 cm
Package 1 Width	10.2 cm
Package 1 Length	23.0 cm
Package 1 Weight	1000.0 g

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.