

Product data sheet

Characteristics

EBX510

ComX 510 - energy server - UL - SDRAM4 Go



Main

Range	PowerLogic
Product name	ComX
Product or component type	Energy server
Device short name	ComX 510

Complementary

[Us] rated supply voltage	Main supply: 24 V DC
Maximum power consumption in W	26 W 24 V 15 W via PoE
Communication network type	RS485, Modbus serial on 1 RJ45 RS485, Modbus serial on terminal block Ethernet, PoE 15W (Power over Ethernet) on 1 RJ45 Ethernet, DHCP on 1 RJ45
Number of inputs	6 digital 2 analog
Discrete input current	60 mA at 12 V DC
Sensor power supply	24 V DC at 50 mA
Analogue input type	Pt 1000 Pt 100 0...10 V 4...20 mA
Communication gateway	Ethernet TCP/IP to Modbus
Memory capacity	128 MB RAM 256 MB flash 4 GB SDRAM
Mounting mode	Clip-on
Mounting support	35 mm DIN rail
Product certifications	C-Tick CUL UL CE
Standards	EN 60950 EN 61010-1 UL 508 UL 60950
Depth	69 mm
Height	109 mm
Width	144 mm
Net weight	450 g
Product specific application	Energy management systems

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Web services	Web server
Local signalling	LED: for power supply LED: for status (GPRS) LED: for communication (Modbus) LED: for communication (Ethernet) LED: for communication (WiFi) LED: for I/O

Environment

Relative humidity	5...95 % at 55 °C without condensation
IP degree of protection	IP20 (terminal block) IP40 (front face)
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Pollution degree	3
Operating altitude	2000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	449 g
Package 1 Height	8 cm
Package 1 width	11 cm
Package 1 Length	16 cm
Unit Type of Package 2	S03
Number of Units in Package 2	15
Package 2 Weight	7.222 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins