

## Product data sheet

### Characteristics

# EVA1RFKES

Enclosure, EVlink Pro AC, Metal, IP66, pedestal mount in metallic kit enclosure, for 25mm<sup>2</sup> to 35mm<sup>2</sup> cable



### Main

Range	EVlink
Product name	EVlink Pro AC Metal
Product or component type	Enclosure
Range compatibility	EVlink EVlink Pro AC EVB3 charging station
Poles description	3P + N
Mounting mode	Assembled
Localisation on device	On lower part
Rated supply voltage	380...415 V AC 50/60 Hz 220...240 V AC 50/60 Hz
Earthing system	TT TN-S TN-C-S IT Compatible IT with additional isolation transformer on the power supply

### Complementary

Provided equipment	1 mounting plate 2 DIN rail 4 fixing bracket 3 cable gland
DIN rail length	240 mm
Mounting plate description	Telequick perforated
Cable entry number	2 cable gland for M32 1 cable gland for M12
Cable cross section	25...35 mm <sup>2</sup>
Height	360 mm
Width	270 mm
Depth	180 mm
Product weight	3.4 kg

### Environment

IP degree of protection	IP66
IK degree of protection	IK09
Ambient air temperature for operation	-30...70 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.000 cm
Package 1 Width	29.000 cm
Package 1 Length	38.500 cm
Package 1 Weight	3.253 kg
Unit Type of Package 2	P12

Number of Units in Package 2	40
Package 2 Height	110.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	153.500 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations