

## Product data sheet

### Characteristics

# EVP1CBS321A45

## Attached cable T1 32A 1-Ph IEC 4,5m Smart Wallbox



### Main

Range	EVlink
Product or component type	Charging cable
Accessory / separate part category	Spare part
Network number of phases	Single phase
Poles description	1P + N
[In] rated current	32 A
[Us] rated supply voltage	220...240 V AC 50/60 Hz
Earthing system	Compatible IT with additional isolation transformer on the power supply Compatible TN Compatible TT
Nominal output power	7.4 W 32 A
Socket number	1

### Complementary

Connector type	T1 vehicle end silver plated contacts Without connector charging station end
Range compatibility	EVlink (EVlink Smart Wallbox) EVB1 charging station
Standards	IEC 62196-1 IEC 62196-2
Product certifications	CE
Length	4.5 m
Net weight	2.6 kg

### Environment

IP degree of protection	IP54 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	15.0 cm
Package 1 Width	30.0 cm
Package 1 Length	40.0 cm
Package 1 Weight	1.671 kg
Unit Type of Package 2	S02
Number of Units in Package 2	1
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm

Package 2 Weight	2.126 kg
Package 3 Height	80 cm

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>