

Product data sheet

Characteristics

EY56P315

Easy56, Plug, 3 Pin, 15A, 250V



Main

Product name	Easy56
Product or component type	Plug
Device short name	EY56P315
Plug, socket category	Low voltage
Poles description	1P + N + E
Pin number	3 pins
Shape of pin	Flat
Outlet standard	Australian/New Zealand

Complementary

Plug, socket, control station shape	Straight
[In] rated current	15 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50 Hz
Material	Polycarbonate: housing
Contacts material	Pins: brass
Connections - terminals	Screw terminals
Cable cross section	1.5 mm ²
Cable outer diameter	7.4...10.6 mm
Wire stripping length	12...34 mm
Cable entry	Cable gland
Thread type	M20
Net weight	0.107 kg
Height	67 mm
Width	67 mm
Depth	112.5 mm
Colour	Plug: orange (RAL 2004) Body: clear

Environment

Standards	AS/NZS 3112
Quality labels	RCM
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	8.1 cm
Package 1 Length	11.2 cm
Package 1 Weight	112 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations