

Product data sheet

Characteristics

EY56SW132

Easy56, Switch, 1P, 32A, 250V



Main

Product name	Easy56
Device short name	EY56SW132
Product or component type	Switch
Poles description	1P
Control type	Rotary knob
Rotary handle padlocking	2 padlocks 8 mm

Complementary

[Ue] rated operational voltage	250 V AC 50 Hz
[Uimp] rated impulse withstand voltage	2.5 kV conforming to IEC 60947-3 2.5 kV conforming to AS/NZS 3133
[Ithe] conventional enclosed thermal current	32 A
[Ie] rated operational current	32 A (AC-21A) at 250 V AC 32 A (AC-23A) at 250 V AC
Making capacity	320 A at 250 V AC-21A 320 A at 250 V AC-23A
[Icm] rated short-circuit making capacity	1 kA at 250 V AC-21A 1 kA at 250 V AC-23A
[Icw] rated short-time withstand current	1.5 kA at 250 V duration: 1 s
Breaking capacity	0.2 kA at 250 V (AC-21A) 0.2 kA at 250 V (AC-23A)
Suitability for isolation	Yes
Connections - terminals	Screw terminals cable(s) 1...16 mm ² rigid or stranded
Height	101 mm
Width	101 mm
Depth	101 mm
Net weight	0.471 kg
Colour	Body: grey (RAL 7035) Rotary handle: dark grey



Environment

Standards	AS/NZS 3133
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	10.6 cm
Package 1 Length	10.6 cm
Package 1 Weight	483.6 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Not compliant
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration