

## Product data sheet

### Characteristics

# GV4AS487

MX - voltage release - 380...415V AC 50Hz -  
440...480V AC 60Hz - for TeSys GV4



### Main

Range	TeSys
Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	TeSys GV4 TeSys BV4
Voltage release type	Shunt trip release
[Uc] control circuit voltage	440...480 V AC 60 Hz 380...415 V AC 50 Hz

### Complementary

[Ui] rated insulation voltage	480 V conforming to IEC 60947-1
Threshold tripping voltage	0.7...1.1 Un failsafe opening < 0.7 Un possible opening
Impulse duration	>= 20 ms
Mounting mode	Internal mounting
Maximum inrush power in VA	6 VA
Maximum hold-in power consumption in VA	10 VA
Mechanical durability	20000 cycles
Operating time	< 50 ms
Connections - terminals	Spring terminals 1 0.5...1.5 mm <sup>2</sup> - cable stiffness: flexible without cable end
Wire stripping length	8 mm

### Environment

Quantity per set	Set of 1
------------------	----------

### Packing Units

Package 1 Weight	0.036 kg
Package 1 Height	0.150 dm
Package 1 width	0.570 dm
Package 1 Length	0.630 dm

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins