


Product data sheet

Characteristics

GV2AF3

TeSys GV2 - Combination blocks - with contactor LC1D09...D38



Main

| | |
|------------------------------------|----------------------|
| Range | Linergy |
| Product name | FT |
| Device short name | GV2AF |
| Product or component type | Combination block |
| Accessory / separate part category | Connection accessory |
| Range compatibility | TeSys GV2 TeSys D |

Complementary

| | |
|--------------------------------|--------------|
| Product compatibility | LC1D09...D38 |
| Poles description | 3P |
| [Ie] rated operational current | 32 A |
| Quantity per set | Set of 10 |
| Net weight | 0.016 kg |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 22 g |
| Package 1 Height | 9.5 cm |
| Package 1 width | 10 cm |
| Package 1 Length | 15 cm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 260 g |
| Package 2 Height | 9.5 cm |
| Package 2 width | 10 cm |
| Package 2 Length | 15 cm |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 140 |
| Package 3 Weight | 4.094 kg |
| Package 3 Height | 30 cm |
| Package 3 width | 30 cm |
| Package 3 Length | 40 cm |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability


| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|


GV2AF01

Combination GV2ME + TeSys k contactor




GV2AF3

Combination GV2ME + TeSys d contactor



| GV2ME + | LC1D09...D18 | LC1D25 and D32 |
|---------|--------------|----------------|
| b | 176.4 | 186.8 |
| c1 | 94.1 | 100.4 |
| c | 99.6 | 105.9 |

Combination GV2P + TeSys d contactor



| GV2P + | LC1D09...D18 | LC1D25 and D32 |
|--------|--------------|----------------|
| b | 176.4 | 186.8 |
| c1 | 100.1 | 106.4 |
| c | 105.6 | 111.9 |
| d1 | 95 | 95 |
| d | 100.5 | 100.5 |